



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER PLATED
5. RATING: 2A 36VDC
6. ELECTRIC LIFE: 200,000
7. INSULATION RESISTANCE: 1,000M Ω MIN @ 500VDC.
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 70°C
11. TRAVEL: 2.0mm
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. ILLUMINATION COLOR: RED
- ▲ 14. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)
15. ILLUMINATION VOLTAGE RATING: 2.0V @ 20mA
16. INGRESS PROTECTION: IP67



— Schematic
OFF - (ON)
DENOTES MOMENTARY FUNCTION



RECOMMENDED PANEL CUT-OUT

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®		OBJECT ID					
B	ECO-100928	ILLUMINATION VOLTAGE TO 2.0V @ 20 mA	04/20/22	MR	TITLE		000026253					
					PVA6FEW4S11							
					SCALE							
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				1:1	DATE	5/29/2020	DR	MW	DWG	T960045	REV	B