




RECOMMENDED  
PANEL CUT-OUT

SCHEMATIC  
OFF - (ON)  
SPST ILLUMINATED  
( ) = MOMENTARY FUNCTION

## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER PLATED
5. RATING: 2A 36VDC
6. ELECTRIC LIFE: 200,000
7. INSULATION RESISTANCE: 1,000MΩ MIN @ 500VDC.
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 70°C
11. TRAVEL: 2.0mm
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. ILLUMINATION COLOR: GREEN
- ▲ 14. ILLUMINATION VOLTAGE RATING: 2.8 - 3.7V @ 20mA
15. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)
16. INGRESS PROTECTION: IP67



 E-SWITCH®

|     |        |                                         |         |    |
|-----|--------|-----------------------------------------|---------|----|
| B   | 24053  | remove anti-rotation notch from housing | 10/2/19 | MW |
| A   | 24003  | New Release                             | 8/16/19 | MW |
| REV | PCR NO | DESCRIPTION                             | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |     |      |           |    |    |     |         |     |
|-------|-----|------|-----------|----|----|-----|---------|-----|
| SCALE | 2:1 | DATE | 8/16/2019 | DR | MW | DWG | T960037 | REV |
|-------|-----|------|-----------|----|----|-----|---------|-----|