

RECOMMENDED
PANEL CUT-OUT




▲ SCHEMATIC
OFF - (ON)
() = MOMENTARY FUNCTION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER PLATED
5. RATING: 2A 36VDC
6. ELECTRIC LIFE: 200,000
7. INSULATION RESISTANCE: 1,000MΩ MIN @ 500VDC.
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 70°C
11. TRAVEL: 2.0mm
12. ▲ DENOTES CRITICAL PARAMETER.
13. ILLUMINATION COLOR: WHITE
14. ILLUMINATION VOLTAGE RATING: 3.1V @ 20mA
15. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)
16. INGRESS PROTECTION: IP67



▲ RING AND SYMBOL
ILLUMINATED
COLOR: WHITE



 E-SWITCH®

OBJECT ID
000026255

TITLE PVA6RP24201

SCALE	2:1	DATE	11/17/2020	DR	MW	DWG	T960047	REV
								B