





RECOMMENDED
PANEL MOUNTING
1-6mm THICKNESS



LED SCHEMATIC



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. OPERATING TEMP: -40°C to 85°C
5. CURRENT RATING: 2mA-20mA
6. LAMP VOLTAGE: 2.8V
7. IP RATING: IP67
8. ▲ DENOTES CRITICAL PARAMETER.
9. HARDWARE SUPPLIED: O-RING AND HEXNUT

| REV | ECO NO | DESCRIPTION | DATE | BY | E-SWITCH® | | | | OBJECT ID |
|-----|------------|---|----------|----|------------------|-----|---------------|-----------|-----------|
| D | ECO-103573 | CORRECT PANEL DIM | 08/05/25 | JS | | | | | 000003252 |
| | | | | | TITLE PVL06FL131 | | | | |
| | | | | | SCALE | 2:1 | DATE | 1/27/2016 | DR |
| | | THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED | | | rc | DWG | 52-PVL06FL131 | | REV D |