



RECOMMENDED PANEL MOUNTING




PANEL THICKNESS	X
0.75-1.25	19.20-19.30
1.25-2.00	19.30-19.40
2.00-3.00	19.50-19.60

SWITCH FUNCTION	
POS. 1	POS. 3
OFF	ON
OPEN	1a - 1



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REF. ONLY
- ▲ 4. RATING: 15A @125VAC; 8A @250VAC cUrUS
6A 250V VDE
- ▲ 5. LAMP COLOR: GREEN LED
6. MATERIAL: CONTACT: COIN SILVER, SILVER PLATED
TERMINAL: COPPER ALLOY W/SILVER PLATE
7. ELECTRICAL LIFE: 10,000 CYCLES
8. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
9. DIELECTRIC STRENGTH: >1,500V AC 1 MIN
10. OPERATING TEMP.: -30°C to 80°C
11. ▲ DENOTES CRITICAL PARAMETER.



▲ LED SPECS	UNITS	GREEN
FORWARD CURRENT	mA	20
FORWARD VOLTAGE	V	1.7 - 2.1
LUMINOUS INTENSITY	mcd	30 typ.

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
B	ECO-101377	update print	11/04/22	MW	TITLE R1966ABLKBLKEPGRN			000016561
					SCALE 2:1	DATE 3/21/2003	DR BGL	DWG M300102
								REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED