






PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-01 [7.56]
1.25-2.0 [0.049-.079]	19.4-01 [7.64]
2.0-3.0 [0.079-.118]	19.8-01 [7.80]



ACTUATOR:  BLACK POS. 1


 BLACK BODY/HOUSING



PANEL CUTOUT
NOT TO SCALE

SWITCH FUNCTION	
POS. 1	POS. 2
<ON>	OFF
1-1a	OPEN

() = MOMENTARY



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4 X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR 8A @ 250VAC
5. MATERIALS: TERMINALS: Silver Plated Copper Alloy CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute >3000 V between poles
10. 2002/95/EC (ROHS) COMPLIANT



TITLE		SCALE		DATE		DR		DWG		REV	
R1966F BLK BLK IF		1.5:1		6/12/07		TN		M304198		A	
DESCRIPTION		DATE		CHKD							
RELEASED FOR PRODUCTION		6/12/07		TN							
REV. ECN No.											
17380											

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED