


RECOMMENDED PANEL MOUNTING


PANEL THICKNESS	X ± 0.05mm
0.75-1.25mm	29.65mm
1.25-2.00mm	30.15mm
2.00-3.00mm	30.50mm




▲ HOUSING
COLOR: BLACK

▲ ROCKER
COLOR: BLACK

▲ LENS
COLOR: GREEN






SWITCH FUNCTION	
POS. 1	POS. 3
ON	OFF
1-1a	OPEN



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERM. NUMBERS FOR REF. ONLY
- RATING: 20A 125VAC, 16A 250VAC UL APPROVED
16A 250VAC VDE APPROVED
- ELECTRICAL LIFE: OVER 10,000 CYCLES
- MECHANICAL LIFE: OVER 30,000 CYCLES
- CONTACT RESISTANCE: <20 mΩ (INITIAL)
- DIELECTRIC STRENGTH: >1500V 1 min
- INSULATION RESISTANCE: >1,000 mΩ @ 500V DC
- ▲ LAMP VOLTAGE: LED 24VDC
- OPERATING TEMPERATURE: TERMINAL SIDE -20°C to 85°C
ROCKER SIDE -20°C to 55°C
- ▲ DENOTES CRITICAL PARAMETER



D	24184	update print, Incandecent to LED	2/5/2020	MW				
C	19899	UPDATE DRAWING	05/06/11	BMA				
B	12754	REVISED RATINGS	02/27/03	CJB	TITLE R4BBLKBLKGRNEF4			
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE 1:1	DATE 3/21/2001	DR CJB	DWG M401126
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					REV D			