


RECOMMENDED PANEL CUT-OUT


SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
NONE	2-1





▲ CIRCUIT: SPST
OFF - ON

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 20A 125VAC [cURus]
16A 250VAC [cURus]
1/3HP 125/250VAC [cURus]
3/4HP 125/250VAC [cURus]
5. ELECTRICAL LIFE: 6,000 CYCLES MIN.
6. INSULATION RESISTANCE: 100M Ω @ 500VDC
7. CONTACT RESISTANCE: 20m Ω MAX.
8. OPERATING TEMP: 0°C to 105°C [cURus]
9. DIELECTRIC STRENGTH: 1,000V AC 1MIN
10. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 11. LAMP VOLTAGE: NON-ILLUMINATED



▲ BODY COLOR: BLACK
▲ ACTUATOR COLOR: BLACK
▲ I/O MARKING COLOR: RED



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-103917	PRINT UPDATE	03/09/26	JS	TITLE RSC141D1A81				000000333
					SCALE	DATE	DR	DWG	REV
					3:2	2/1/2010	CAB	14-RSC141D1A81	E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED