






NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
- ▲ 5. OPERATING FORCE: 160 ± 50 gf
6. TRAVEL: $0.25 +0.2/-0.1$ mm
7. CONTACT RESISTANCE: 50 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: GOLD
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C



▲ ACTUATOR
COLOR: IVORY



D	24550	REMOVE STEP IN HOUSING, CHANGE TEMP	10/19/20	JM
C	19502	CHANGED TOLERANCE	12/07/10	BGL
B	16112	ADD GOLD DOME NOTE	6/6/06	CT
A	12918	RELEASED	3/17/03	AR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

TITLE TL1105RF160R

SCALE
4:1DATE
9/15/1998DR
EBPDWG
P020228REV
D