






CIRCUIT: SPST



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE:  $x.x = \pm 0.4$   
 $x.xx = \pm 0.25$
3. TERM. NOS. FOR REF ONLY
4. RATING: 50 MILLI-AMPS @24VDC
5. TRAVEL: 1.0 +/-0.5mm
6. CONTACT RESISTANCE: 30 MILLIOHMS MAX
7. INSULATION RESISTANCE: 10M OHMS MIN. AT 100VDC
8. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE
- ▲ 9. OPERATING FORCE:  $300 \pm 75$  GF
10. PACKAGING: TUBE, 45 PIECES PER TUBE
11. LIFE CYCLES: 10,000,000 ACTUATIONS
12. ▲ DENOTES CRITICAL PARAMETER
13. 2002/95/EC (ROHS) COMPLIANT



TITLE TL6200XBF300QP

|     |        |             |         |    |
|-----|--------|-------------|---------|----|
| A   | 21031  | New Release | 2/12/13 | rc |
| REV | PCR NO | DESCRIPTION | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|              |                  |          |                |          |
|--------------|------------------|----------|----------------|----------|
| SCALE<br>2:1 | DATE<br>2/8/2013 | DR<br>rc | DWG<br>T060200 | REV<br>A |
|--------------|------------------|----------|----------------|----------|