


GREEN (FORWARD)



GREEN (REVERSE)

SCHEMATIC

ON - (ON)

DPDT ILLUMINATED

() DENOTES MOMENTARY

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. MECHANICAL LIFE: 1,000,000 CYCLES.
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP.: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 20mA 220V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 3.5 $\pm$ 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67, IK08
18. HARDWARE SUPPLIED: O-RING AND HEXNUT

 $23.60^{+0.20}_{-0.00}$
[.929^{+.008}_{-.000} in]

 $\phi 25.00^{+0.20}_{-0.00}$
[.984^{+.008}_{-.000} in]

 PANEL CUT-OUT
 PANEL THICKNESS 1-10mm

 $\phi 28.0$
[1.10 in]

 $\phi 19.80$
[.78 in]

 ▲ L22 GRAPHIC
 ILLUMINATED COLOR:
 GREEN

 ▲ BUTTON FINISH:
 SILVER

 ▲ HOUSING
 STAINLESS STEEL

 M25 x 1.0
 THREAD


 2.0
 [.08 in]
 27.4
 [1.08 in]
 ▲ 35.2
 [1.39 in]

 2.75
 [.11 in]

 .50
 [.020 in]

 13.00
 [.51 in]

 2.80
 [.110 in]

 5.00
 [.197 in]
 10.00
 [.394 in]


REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
A	ECO-100392	NEW RELEASE	09/28/21	MR	TITLE ULV8F2HSL37L22				100118697
					SCALE	DATE	DR	DWG	REV
					1:1	9/23/2021	MJR	T980405	A

 THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED