







▲ R05 BUTTON
TRANSPARENT (B410000)
ILLUMINATED: RED / BLUE



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: x.x = $\pm 0.4\text{mm}$
x.xx = $\pm 0.25\text{mm}$
3. RATING: DC 30V, 0.3A
4. OPERATING FORCE: $200 \pm 100\text{gf}$
5. TRAVEL: 3.3mm FULL TRAVEL
6. LIFE CYCLES: 10,000 CYCLES
7. OPERATING TEMPERATURE: -40°C to 85°C
8. CONTACT RESISTANCE: $20\text{m}\Omega$ MAX.
9. INSULATION RESISTANCE: $100\text{M}\Omega$ MIN@ 500VDC
- ▲ 10. LED COLOR: RED / BLUE
11. ▲ DENOTES CRITICAL PARAMETER

LED SPECS	UNITS	RED	BLUE
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE @ 20mA	V	2.0 Typ - 2.6 Max	3.0 Typ - 3.5 Max
LUMINOUS INTENSITY @ 20mA	MCD	200 typ.	400 typ.

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-101665	pint update	02/15/23	MW

 E-SWITCH®				OBJECT ID 100123590
TITLE WBL2UOARBQR05CLR				
SCALE 2:1	DATE 2/3/2023	DR MW	DWG B400023	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED