



RBF85X12C24C 2

(Part shown, no material (X) specified)


PN	Description
RB85-X12Y	(1) RB85-X12Y, Top
RBF85X24Y	(1) RBF85X24Y, Bottom
8085	(1) RB85 O-Ring
6052	(4) #6-32 X 1.75" Captive Ph Pan Hd Screw
6022	(4) #10 High/Low Pan Hd x 1/4"
6113	(4) #6-32 Threaded Insert

 = INTERIOR DIMENSIONS (@ BOTTOM)

2 =STANDARD COLORS (Y) ARE: BLACK (B), CLEAR (C) AND GRAY (G)
TOPS AND BOTTOMS ALL POSSIBLE COMBINATIONS AVAILABLE
STANDARD MATERIALS (X) IS: POLYCARBONATE (P)

- Watertight enclosure meets or exceed Nema 4 and or IP67.

DIMENSIONS in Inch
[mm]




ALL DIMENSIONS ARE $\pm .010"$ 1/16/2023
2009 Wright Ave., La Verne, Ca. 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

SERPAC

Electronic Enclosures

RBF85 Circuit Board (Fits all Parts starting with RBF85)



(REFERENCE ONLY)