



MATERIAL: BRASS

PLATING: Au/Ni

WIRE SIZE: 20-26 AWG RECOMMENDED

CONTACT CURRENT RATING: 5A MAX.

NOTE #1: CONTACTS SUPPLIED
LOOSE PIECE (500 PER BAG)

	NORCOMP PART NUMBER
250 MATING CYCLES // CLASS 2	170-201-170L003

ONCE INSERTED INTO NORCOMP 170 SERIES CRIMP AND POKE CONNECTORS,
CANNOT BE REMOVE.

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

P. JENKINS

DATE:

07/15/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	SHEET	OF	REV
DWG NO.		1	1	8

170-201-170L003