



DESCRIPTION: 0.750 CENTER DUAL PORT D-SUB - FEMALE OVER MALE

25 PIN  
SHOWN



## SPECIFICATIONS:

### MATERIALS:

|           |                                                |
|-----------|------------------------------------------------|
| HOUSING:  | UL94 V-0 RATED, BLACK PA9T, 260° PROCESS TEMP. |
| CONTACTS: | GOLD PLATED BRASS (SEE P/N KEY BELOW)          |
| SHELL:    | NICKEL PLATED STEEL                            |

### ELECTRICAL:

|                        |                 |
|------------------------|-----------------|
| RATED CURRENT:         | 5A              |
| INSULATOR RESISTANCE:  | 1,000 Ohms MIN. |
| DIELECTRIC STRENGTH:   | 1,000 VAC RMS   |
| WORKING VOLTAGE:       | 250V            |
| OPERATING TEMPERATURE: | -55°C TO +105°C |

### DIMENSIONS:

|   | 9             | 15            | 25            | 37            |
|---|---------------|---------------|---------------|---------------|
| A | 1.204 [30.58] | 1.535 [38.99] | 2.078 [52.78] | 2.724 [69.19] |
| B | 0.984 [24.99] | 1.312 [33.32] | 1.850 [46.99] | 2.500 [63.50] |
| C | 0.494 [12.55] | 0.494 [12.55] | 0.494 [12.55] | 0.494 [12.55] |

178-YYY-313R451

|                  |                                                                                                                                        |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| SERIES           | 178                                                                                                                                    |
| POSITIONS        | YYY                                                                                                                                    |
| 009              |                                                                                                                                        |
| 015              |                                                                                                                                        |
| 025              |                                                                                                                                        |
| 037              |                                                                                                                                        |
| GENDER           | 31 = FEMALE OVER MALE<br>41 = MALE OVER FEMALE<br>51 = FEMALE OVER FEMALE<br>61 = MALE OVER MALE                                       |
| SHELL PLATING    | 3 = NICKEL                                                                                                                             |
| HARDWARE OPTIONS | 45 = 4-40 INSERTS/METAL BRACKET                                                                                                        |
| PLATING OPTIONS  | 1 = SELECTIVE (GF MATING AREA / TIN PLATED TAILS)<br>A = 30u" GOLD MATING AREA/GOLD FLASH TAILS<br>9 = 30u" GOLD MATING AREA/TIN TAILS |

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
C. SMITH

DATE:  
03/30/07

NorComp

SCALE:  
NTS

SHEET 1 OF 1

REV  
8

DWG NO.

178-YYY-313R451