

## NOTE:

## MATERIAL

HOUSING: PBT UL94V-0, BLACK  
 CONTACT: BRASS  
 NUT: BRASS  
 SHELL: BRASS

## FINISH

CONTACT: 10 $\mu$ " GOLD PLATED  
 OVER NICKEL  
 NICKEL PLATED  
 NICKEL PLATED

## NUT:


## SHELL:

## ELECTRICAL

RATED CURRENT: 1.5A  
 RATED VOLTAGE: 30V  
 WATER PROOF: IP67  
 MAX WIRE AWG: 24

## ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
 THE PROPERTY OF NorComp AND SHALL NOT  
 BE REPRODUCED, COPIED OR USED AS THE  
 BASIS FOR THE MANUFACTURE OR SALE OF  
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
J. KADELDATE:  
03/08/2021

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	SHEET	OF	REV
DWG NO.		1	1	1

854-B05-103RLS4