

## NOTE:

## MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

SHELL:

BRASS

## FINISH

CONTACT:

10μ" GOLD PLATED

OVER NICKEL

NICKEL PLATED

NUT:

NICKEL PLATED

## ELECTRICAL

RATED CURRENT:

1.5A

RATED VOLTAGE:

30V

WATER PROOF:

IP67


MAX WIRE AWG:

24

## ENVIRONMENT

OPERATION TEMPERATURE:

-40°C TO +85°C



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
J. KADELDATE:  
03/08/2021

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	OF	REV
DWG NO.	854-B05-203RLS4	1	1