

SPECIFICATIONS:

MATERIALS:


HOUSING:	PBT, UL94 V-0, BLACK
CONTACTS:	10u" GOLD PLATED BRASS
NUT:	NICKEL PLATED BRASS
SHELL:	NICKEL PLATED BRASS
ORING:	NBR

ELECTRICAL:

RATED CURRENT:	3A (3/4P)
RATED VOLTAGE:	60V (3/4P)
INSULATION RESISTANCE:	100 MOhms MIN.
CONTACT RESISTANCE:	10 mOhms MAX.


ENVIRONMENT:

OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67
MAX WIRE AWG:	24 AWG



854-YYY-203RSS4

003 = 3 POSITION
004 = 4 POSITION



MATING SIDE VIEW

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
J. KADELDATE:
09/12/2023

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	1	REV
DWG NO.		1	1

854-YYY-203RSS4