



NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK
CONTACT: BRASS
NUT: BRASS
O-RING: EPDM, BLACK

FINISH

CONTACT: GOLD PLATED
UNDER PLATE: NICKEL
NUT: NICKEL PLATED
60 μ TO 100 μ OVER ALL

ELECTRICAL

RATED CURRENT: 4A
RATED VOLTAGE: 250V
INSULATION RESISTANCE: 100 M Ω hms MIN.
CONTACT RESISTANCE: 10 m Ω hms MAX.

WATER PROOF:

ENVIRONMENT
OPERATION TEMPERATURE: -40°C TO +85°C
MAX WIRE AWG: 20

858-004-203RSUY

3 = BRASS/NICKEL NUT
S = STAINLESS STEEL NUT

1 = GOLD FLASH
4 = 10 μ GOLD

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON

DATE: 03-07-16

SCALE: NTS

SHEET 1 OF 1

REV 4

NorComp

DWG NO.

858-004-203RSUY