

## MATERIALS:



|             |                              |
|-------------|------------------------------|
| HOUSING:    | PBT, UL94 V-0, BLACK         |
| CONTACTS:   | 10 $\mu$ " GOLD PLATED BRASS |
| NUT:        | NICKEL PLATED ALUMINUM ALLOY |
| SHELL:      | NICKEL PLATED ALUMINUM ALLOY |
| MAIN BODY:  | NICKEL PLATED ALUMINUM ALLOY |
| GLAND:      | SILICONE, BLACK              |
| GLAND CAGE: | POM, WHITE                   |
| GLAND NUT:  | NICKEL PLATED ALUMINUM ALLOY |
| ORING:      | SILICONE, BLACK              |

## ELECTRICAL:

|                        |                        |
|------------------------|------------------------|
| RATED CURRENT:         | 4A                     |
| RATED VOLTAGE:         | 250V                   |
| INSULATION RESISTANCE: | 100 M $\Omega$ ms MIN. |
| CONTACT RESISTANCE:    | 10 m $\Omega$ ms MAX.  |

## ENVIRONMENT:

|                        |                |
|------------------------|----------------|
| OPERATING TEMPERATURE: | -40°C TO +85°C |
| WATER PROOF:           | IP67           |
| MAX WIRE AWG:          | 20 AWG         |



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

J. KADEL

DATE:

12/11/2023

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:

NTS

DWG NO.

SHEET 1 OF 1

REV 0

858-B04-103RKT4