

## SPECIFICATIONS:

## MATERIALS:

HOUSING: PBT, UL94 V-0, BLACK  
 CONTACTS: GOLD PLATED BRASS  
 (SEE PART NUMBER KEY)  
 NUT: NICKEL PLATED BRASS  
 ORING: EPDM




## ELECTRICAL:

RATED CURRENT: 4A  
 RATED VOLTAGE: 250V  
 INSULATION RESISTANCE: 100 M $\Omega$ ms MIN.  
 CONTACT RESISTANCE: 10 m $\Omega$ ms MAX.

## ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C  
 WATER PROOF: IP67

MAX WIRE AWG: 20



**858-R03-203RSUY**

3 = BRASS/NICKEL NUT  
 S = STAINLESS STEEL NUT

1 = GOLD FLASH  
 4 = 10 $\mu$ " GOLD

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
 THE PROPERTY OF NorComp AND SHALL NOT  
 BE REPRODUCED, COPIED OR USED AS THE  
 BASIS FOR THE MANUFACTURE OR SALE OF  
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
 J. KADEL

DATE:  
 09/22/2020

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

**NorComp**

SCALE:	NTS	1	REV
DWG NO.		1	2
		858-R03-203RSUY	