

CONNECTOR 1

1. CONNECTOR 1 : 858-004-103RSS4, MOLDED STRAIGHT HOOD, COLOR BLACK
2. WIRE : 24AWG, 4 TWISTED PAIRS, UL2835, FOIL SHIELD, COLOR BLACK, 30V
3. CABLE DIAMETER : 6.50mm±0.19
4. PIN OUT :

WIRING SCHEMATIC

Pin #1	—	BLUE
Pin #2	—	BLUE/WHITE
Pin #3	—	ORANGE
Pin #4	—	ORANGE/WHITE
SHELL	SHIELD	

CCA-000-MYYR198

01	=	1 METER
02	=	2 METERS
03	=	3 METERS
06	=	6 METERS

**SEE PAGE 3 FOR CABLE
SPECIFICATIONS

RoHS COMPLIANT

UNITS = "as indicated"

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
DATE:
04-22-15

NorComp

SCALE:	NTS	SHEET 1	OF 3	REV 6
DWG NO.				

CCA-000-MYYR198



RoHS COMPLIANT

UNITS = mm

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 04-22-15


NorComp

SCALE: NTS	SHEET 2 OF 3	REV 6
DWG NO. CCA-000-MYYR198		

ELECTRICAL CHARACTERISTICS



VOLTAGE RATING : 30V
 TEMPERATURE RATING : 60°C
 SPARK TEST : AC-2000V/0.15 sec MIN.
 DIELECTRIC STRENGTH : AC-750V/1 sec MIN.
 INSULATION RESISTANCE : PE: DC-500V 15000 MΩHM/100M MIN. AT 20°C
 CONDUCTOR RESISTANCE : 24AWG - 93.2 ΩHM/KM MAX. AT 20°C



COLOR CODE

1. BROWN * BROWN/WHITE
2. BLUE * BLUE/WHITE
3. ORANGE * ORANGE/WHITE
4. GREEN * GREEN/WHITE

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMONDATE:
04-22-15

NorComp

SCALE:
NTS
DWG NO.SHEET OF
3 3
REV
6
CCA-000-MYYR198