


1. CONNECTOR 1 : 854-AX4-103RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
2. CONNECTOR 2 : 854-AX4-103RLS4, MOLDED STRAIGHT HOOD, COLOR BLACK
3. WIRE : 26AWG, 2 1/2 TWISTED PAIRS, UL20276, FOIL/BRAID/DRAIN SHIELD, COLOR BLACK, 30V
4. SHIELDING : 360°
5. CABLE DIAMETER : 4.60mm±0.15mm
6. PIN OUT :

### WIRING SCHEMATIC



NORCOMP P/N	LENGTH	TOLERANCE
CCA-000-M01R189	1M	±12mm
CCA-000-M02R189	2M	±25mm
CCA-000-M03R189	3M	±25mm
CCA-000M.21R189	200mm	±12mm

\*\*SEE PAGE 3 FOR CABLE  
SPECIFICATIONS

**RoHS COMPLIANT**

UNITS = mm

DO NOT SCALE FROM DRAWING





THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 04-13-15

**NorComp**

SCALE: NTS SHEET 1 OF 3 REV 6  
DWG NO.

CCA-000-MYYR189



RoHS COMPLIANT

UNITS = mm



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 04-13-15

DO NOT SCALE FROM DRAWING



NorComp

SCALE: NTS	SHEET 2	OF 3	REV 6
---------------	------------	---------	----------

DWG NO. CCA-000-MYYR189

## ELECTRICAL CHARACTERISTICS

VOLTAGE RATING : 30V  
 TEMPERATURE RATING : 80°C  
 SPARK TEST : AC-500V/0.15 sec MIN.  
 DIELECTRIC STRENGTH : AC-750V/1 sec MIN.  
 INSULATION RESISTANCE : SR-PVC: DC-500V 10 MΩHM/KM MIN. AT 20°C  
 CONDUCTOR RESISTANCE : 26AWG-153 ΩHM/KM MAX. AT 25°C



## COLOR CODE

1. BLACK \* BROWN (P570 & P571)
2. RED \* ORANGE (P572 & P573)
3. YELLOW (574)

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON

DATE: 04-13-15

NorComp

SCALE: NTS  
DWG NO.SHEET 3 OF 3  
REV 6  
CCA-000-MYYR189

DO NOT SCALE FROM DRAWING