


DESCRIPTION: 15 POS MICRO-D FEMALE (ASSEMBLED) TO BLUNT CUT

THUMBSCREWS: NICKEL PLATED STEEL - UNC #2-56 THREAD



1. P1: NORCOMP p/n 960-015-010R011
2. P2: BLUNT CUT END
3. WIRE: 28AWG [7X36] x15C +ALUMINUM FOIL W/BRAID 65%, UL2464, COLOR BLACK
4. PINOUT:

P1	P2
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GRAY
10	WHITE
11	PINK
12	LIGHT GREEN
13	BLACK WHITE
14	BROWN WHITE
15	RED WHITE
SHELL	SHIELD

NOTE:

NOT DESIGNED TO MATE WITH NORCOMP 580-M // 581-M SERIES CONNECTORS.
IF ANY QUESTIONS PLEASE CONTACT ENG@NORCOMP.NET

P/N	L ± T
CCA-015-F18R152	216±2.952in
CCA-015-F28R152	336±3.952in
CCA-015-I18R152	18±0.590in
CCA-015-I36R152	36±0.787in
CCA-015-I72R152	72±0.984in
CCA-015-M.5R152	500±15mm
CCA-015-M01R152	1000±20mm
CCA-015-M02R152	2000±25mm
CCA-015-M10R152	10000±100mm
CCA-015-M15R152	15000±100mm
CCA-015-M20R152	20000±150mm
CCA-015-M30R152	30000±250mm

RoHS COMPLIANT

PACKAGED: 1 PER BAG

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NORCOMP AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

P. JENKINS

DATE:

01/18/2012

NorComp

SCALE:
NTS

SHEET
1

OF
1

REV
8

DWG NO.
CCA-015-YYYR152