

\*\*SEE PAGE 2 FOR CONNECTOR DETAILS

WIRING SCHEMATIC	
1	2
PIN	PIN
1 = BROWN	1 = RED
2 = WHITE	2 = GREEN
3 = BLUE	3 = BLACK
4 = BLACK	4 = WHITE

FPM12A04IYYDR0Y  
 INCHES  
 01 = WIRING SCHEMATIC 1  
 02 = WIRING SCHEMATIC 2  
 LENGTH  
 EX: 06 = 6 INCHES  
 12 = 12 INCHES

Full stainless steel variant successfully passes  
 96-hour salt spray testing per ASTM B117

NOTE: PACKAGED 10 PER BAG

**RoHS COMPLIANT**



THESE DRAWINGS AND SPECIFICATIONS ARE  
 THE PROPERTY OF NorComp AND SHALL NOT  
 BE REPRODUCED, COPIED OR USED AS THE  
 BASIS FOR THE MANUFACTURE OR SALE OF  
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
 G. BROWN  
 DATE:  
 01/23/2019

UNITS = "as indicated" **DO NOT SCALE FROM DRAWING**

**NorComp**

SCALE: NTS	SHEET 1 OF 2	REV 4
DWG NO. FPM12A04IYYDR0Y		

**MATERIALS:**

HOUSING:

PBT, UL94 V-0, BLACK

CONTACTS:

10 $\mu$ "GOLD PLATED BRASS

NUT:

316 STAINLESS STEEL

SHELL:

316 STAINLESS STEEL

ORING:

EPDM, BLACK

**ELECTRICAL:**



RATED CURRENT: 4A

RATED VOLTAGE: 250V



INSULATION RESISTANCE: 100 M $\Omega$ ms MIN.CONTACT RESISTANCE: 10 m $\Omega$ ms MAX.**ENVIRONMENT:**

OPERATING TEMPERATURE: -40°C TO +85°C

WATER PROOF: IP67 / IP68



NUT

RECOMMENDED PANEL CUT-OUT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
G. BROWN  
DATE:  
01/23/2019

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 2	OF 2	REV 4
---------------	------------	---------	----------

DWG NO. FPM12A04IYYDR0Y