

SPECIFICATIONS:

MATERIALS:

HOUSING:

PBT, UL94 V-0

CONTACTS:

GOLD FLASH PLATED BRASS

SHELL:

TIN PLATED STEEL

ELECTRICAL:

RATED CURRENT:

3A

WORKING VOLTAGE:

250V

INSULATION RESISTANCE:



1000 MOhms MIN.

CONTACT RESISTANCE:

15 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE: -55°C TO +105°C



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH
DATE:
10/12/2007

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 4
DWG NO. GCHDLP15M15M		