

## SPECIFICATIONS:

## MATERIALS:

HOUSING:

PBT, UL94 V-0

CONTACTS:

GOLD FLASH PLATED BRASS

SHELL:

TIN PLATED STEEL

## ELECTRICAL:

RATED CURRENT:

3A

WORKING VOLTAGE:

250V

INSULATION RESISTANCE:






1000 MΩHMS MIN.

CONTACT RESISTANCE:

15 mΩHMS MAX.

## ENVIRONMENT:

OPERATING TEMPERATURE: -55°C TO +105°C



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
C. SMITH  
DATE:  
10/12/2007

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1 OF 1	REV 1
DWG NO. GCHDLPF15M15F		