

## SPECIFICATIONS:

## MATERIALS:



HOUSING: PBT, UL94 V-0  
CONTACTS: GOLD FLASH PLATED BRASS  
SHELL: TIN PLATED STEEL

## ELECTRICAL:

RATED CURRENT: 3A  
WORKING VOLTAGE: 250V  
INSULATION RESISTANCE: 1000 MOhms MIN.  
CONTACT RESISTANCE: 15 mOhms MAX.

## ENVIRONMENT

OPERATING TEMPERATURE: -55°C TO +105°C



UNITS = inch [mm]

**DO NOT SCALE FROM DRAWING**

NC

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

# NorComp

SCALE: **NTS** SHEET **1** OF **1** REV **2**

DWG NO.

GCHDLPF15M15M