


DESCRIPTION: 9P MALE / 9P MALE GENDER CHANGER



SPECIFICATIONS:

MATERIALS:

HOUSING:

PBT, UL94 V-0

CONTACTS:

GOLD FLASH PLATED BRASS

SHELL:

TIN PLATED STEEL

ELECTRICAL:

RATED CURRENT: 5A

250V



WORKING VOLTAGE: 1000 MOhms MIN.

INSULATION RESISTANCE: 15 mOhms MAX.

CONTACT RESISTANCE: 15 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE: -55°C TO +105°C



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
C. SMITH

DATE:  
10/12/2007

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

| SCALE: NTS         | SHEET 1 OF 1 | REV 3 |
|--------------------|--------------|-------|
| DWG NO. GCLP09M09M |              |       |