

注記

NOTES:

1. MATERIAL

ウェハー：ポリアミド, UL94V-0 (色: アイボリー)

WAFER: POLYAMIDE, UL94V-0 (COLOR: IVORY)

ピン: □0.635 黄銅

PIN: □0.635 BRASS

PLATING：錫めっき(5 micro-meters MIN)、銅下地(2.5 micro-meters MIN)

TIN PLATING (5 micro-meters MIN),

COPPER UNDER PLATING (2.5 micro-meters MIN)

△2

6極以上に適合。


TO BE APPLIED FOR 6 CKT. AND ABOVE.

△3

5極以下はロック部スリットなし。

NO SLIT IS PROVIDED FOR 5 CKT. AND LESS THAN 5CKT.

公差非累積
NON-ACCUMULATIVE



基板取付穴推奨寸法
RECOMMENDED P.C. BOARD HOLE DIM.

1	2.5	2.5	22044025	5045-02F	2
(C)	(B)	(A)	ORDER NO.	PARTS NO.	CKT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515931			molex							
mm		5:1												
GENERAL TOLERANCES (UNLESS SPECIFIED)				MINI-LATCH 2.5 HEADER ASSEMBLY VT FLANGE PIN TYPE TIN PLATING										
ANGULAR TOL ± 3.0 °														
4 PLACES		± 0.4		EC NO: 812933 DRWN: MADHAM5 2025/01/23 CHK'D: GGA 2025/03/03 APPR: GGA 2025/03/03			PRODUCT CUSTOMER DRAWING							
3 PLACES		± 0.4												
2 PLACES		± 0.4												
1 PLACE		± 0.4		INITIAL REVISION: DRWN: SOBARA01 2017/04/25 APPR: TKANEKO 2017/05/24			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION			
0 PLACES		± 0.4					50450000		PSD	000	B1			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	SHEET NUMBER	
						A3-SIZE		5045		SEE CHART		GENERAL		1 OF 1

