





9	WRAP LABEL	VINYL	YELLOW
8	OVERMOLD	TPC	YELLOW
7	O-RING	NITRILE	RED
6	COUPLING NUT, FEMALE THD (-2 OPT)	DELRIN	WHITE
5	COUPLING NUT, FEMALE THD (-1 & -8 OPT)	ST. STEEL	PASSIVATED
4	COUPLING NUT, FEMALE THD (STD OPT)	ZINC DIE CAST	BLACK
3	CONTACT SOCKET	COPPER ALLOY	GOLD PLATED
2	FEMALE INSERT	NYLON	BLACK
1	CABLE, 22 AWG, SHIELDED	PVC JACKET	YELLOW
ITEM	DESCRIPTION	MATERIAL	FINISH

DOCUMENT STATUS	P1	RELEASE DATE	2024/08/21	17:05:16
-----------------	----	--------------	------------	----------

MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH	POLES	CABLE DIA
1200720056	702000D02F010	1 FT	2	0.20 [5.1]
1200720179	703000D02F1201	12 FT	3	0.23 [5.8]
1200720368	704000D02F2502	25 FT	4	0.22 [5.6]
1200720488	705000D02M380	38M	5	0.24 [6.1]
1200720571	706000D02F0608	6 FT	6	0.25 [6.4]

FUNCTIONAL SYMBOLS

FA=0

FC=0

FP=0

DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

INCH/MM

SCALE

NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±----	±----
3 PLACES	±----	±----
2 PLACES	±----	±----
1 PLACE	±----	±----
0 PLACES	±----	±----

CURRENT REV DESC: ADDED POLE COUNT, UL, CSA & CABLE DIA IN PN TABLE. ITEM-9 FINISH WAS BLACK/YELLOW

EC NO: 795982

DRWN: ABENJAMINLW 2024/08/20

CHK'D: PDODDAMANEMY 2024/08/21

APPR: BWOODMAN 2024/08/21

INITIAL REVISION:

DRWN: RSTONE 2017/07/14

APPR: BWOODMAN 2017/07/21

ANGULAR TOL ± ---- °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

C-SIZE

SERIES

120072

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

1 OF 1

DOCUMENT NUMBER

SD-120072-022

DOC TYPE|DOC PART| REVISION

PSD 001 B1

molex

MIC CORD ASSY 2-6 POLE

FEMALE, DUAL KEY 22 AWG SHIELDED PVC

PRODUCT CUSTOMER DRAWING