




10	WRAP LABEL	VINYL	BLACK ON YELLOW
9	OVERMOLD	TPE	YELLOW
8	COUPLING NUT, MALE	ZINC DIE CAST	E-COAT BLACK
7	CONTACT PIN	COPPER ALLOY	GOLD
6	MALE INSERT (CENELEC)	TPE	YELLOW
5	COUPLING NUT, FEMALE	ZINC DIE CAST	E-COAT BLACK
4	FRICTION RING	NYLON	WHITE
3	CONTACT SOCKET	COPPER ALLOY	GOLD
2	FEMALE INSERT (CENELEC)	TPE	YELLOW
1	CABLE 16-4 TC/ER	TPE JACKET	YELLOW
ITEM	DESCRIPTION	MATERIAL	FINISH

NOTES:
1. MATERIAL: AS NOTED
2. FINISH: AS NOTED
3. ELECTRICAL:
VOLTAGE: 600V
CURRENT: 8A
4. TEMP RATING: -20° TO +90°C
5. PROTECTION: IP67 (WHEN MATED)
6. ALL DIMS ARE FOR REFERENCE UNLESS TOLERANCED OR NOTED OTHERWISE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: INITIAL CREATION									
	INCH/MM		1:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
	DIVISIONAL SYMBOLS			MM	INCH	EC NO: 752666 DRWN: HENRYB1 2023/06/12 CHK'D: RSTONE 2023/06/27 APPR: BWOODMAN 2023/06/27 INITIAL REVISION: DRWN: HBIZNEK 2023/06/12 APPR: BWOODMAN --/--/-- THIRD ANGLE PROJECTION DRAWING B-SIZE SERIES 130010								
4 PLACES		±	±											
3 PLACES		±	±											
2 PLACES		±	±											
	1 PLACE		±	±	PRODUCT CUSTOMER DRAWING									
	0 PLACES		±	±										
	ANGULAR TOL		±	°										
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
					DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
					1300109039				PSD		000		A	
					MATERIAL NUMBER				CUSTOMER				SHEET NUMBER	
													1 OF 1	