



PART NO	ENGINEERING NO.	FINISHED LENGTH
1300660029	1R3000A28A060G	6IN [0.5 FT]
1300660038	1R3000A28M020G	2M [6 FT 7 IN]
1300660301	1R3000A28M060G	6M [19 FT 2 IN]




FEMALE-FACE VIEW



REF. KNOCKOUT HOLE

- NOTES:
1. MATERIAL: AS NOTED
 2. FINISH: AS NOTED
 3. ELECTRICAL:
VOLTAGE: 500V PER IEC60664
600V PER UL2237
CURRENT: 20A (C1)
 4. TEMP RATING: -20°TO +105°C
 5. PROTECTION: IP67 (WHEN MATED)
 6. COUPLING THREAD: 7/8-16UN
 7. UL LISTED FILE: E258922
 8. ALL DIMENSIONS ARE FOR REFERENCE
UNLESS TOLERANCED OR NOTED OTHERWISE

6	FLAG LABEL	VINYL	BLACK/YELLOW
5	POTTING MATERIAL	EPOXY	BLACK
4	WIRE, 14 AWG (UL1015)	PVC INSULATION	SEE FACE VIEW
3	CONTACT SOCKET	COPPER ALLOY	GOLD PLATED
2	FEMALE INSERT	TPE	BLACK
1	RECEPTACLE SHELL	ZINC DIE-CAST	NICKEL PLATED
ITEM	DESCRIPTION	MATERIAL	FINISH



PART NO. MATRIX
1R3000A28M060G

FINISHED LENGTH:
A060= 6 IN.
F020= 2 FEET
M005= 0.5 METER
M010= 1 METER
M100= 10 METER

CABLE LENGTH TOLERANCES			
<.3M [1FT]: +19mm-0 [+.75in-0]			
.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]			
.9 - 1.8M [3 - 6FT]: +55.6mm-0 [+2.19in-0]			
1.8 - 3.7M [6 - 12FT]: +88.9mm-0 [+3.50in-0]			
3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]			
7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]			
14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]			
OVER 30M [100FT] +2% OF FINISHED LENGTH			

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: UPDATED CURRENT TO 20A			molex							
	INCH/MM		NTS												
	F A =0	GENERAL TOLERANCES (UNLESS SPECIFIED)				BRAD POWER RECEPTACLE A-SIZE 3 POLE, FEMALE, STRAIGHT, SINGLE KEY, #14 AWG									
F E =0															
F P =0	mm		INCH		EC NO: 794205 DRWN: HENRYB12024/08/02 CHK'D: ALEON012024/08/02 APPR: BWOODMAN2024/10/21										
4 PLACES		±----	±----												
DIVISIONAL SYMBOLS	3 PLACES		±----	±----	INITIAL REVISION: DRWN: RSTONE2017/01/11 APPR: BWOODMAN2017/01/26										
	2 PLACES		±----	±----											
	1 PLACE		±----	±----	PRODUCT CUSTOMER DRAWING										
	0 PLACES		±----	±----											
	ANGULAR TOL ± ---- °					DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION				
					SD-130066-075			PSD	001	C1					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						B-SIZE		130066		SEE CHART		GENERAL MARKET		1 OF 1	