




COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



RoHS compliant
by exemption



PCB hole pattern, mounting side



Permeability is not tested.

No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
6	2	Snap-in rivet	PCB 1.6mm / Brass	tin plated
5	2	Threaded spacer	MW 4-40 / Brass	tin plated
4	2	Bracket	F1080-27 / Brass	tin plated
3	8	High power contact	FMP009S104R	40A
2	1	Shell	Brass	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	green

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
$\nabla = 0$	DIMENSION UNITS	SCALE	MEASUREMENTS WITHOUT TOLERANCE ACC. TO		
$\nabla = 0$	mm	2:1	ISO 2768-m	PRODUCT CUSTOMER DRAWING	
$\nabla = 0$				MATERIAL NUMBER	
				1731140641	
				REVISION	
				2	
				DOCUMENT NUMBER	
				FM8W8S-5115	
				CUSTOMER	
				GENERAL MARKET	
				SHEET NUMBER	
				1 OF 1	