


12		11		10		9		8		7		6		5		4		3		2		1	
H				39-30-9245	5566-24AGS2-210	39-29-6248	5566-24AGS-210											39-28-8240	5566-24A-210	24			
				39-30-9225	5566-22AGS2-210	39-29-6228	5566-22AGS-210											39-28-8220	-22A-210	22			
				39-30-9205	5566-20AGS2-210	39-29-6208	5566-20AGS-210											39-28-8200	-20A-210	20			
				39-30-9185	5566-18AGS2-210	39-29-6188	5566-18AGS-210											39-28-8180	-18A-210	18			
				39-30-9165	5566-16AGS2-210	39-29-6168	5566-16AGS-210	39-30-6162	5566-16AS-210									39-28-8160	-16A-210	16	H		
				39-30-9145	5566-14AGS2-210	39-29-6148	5566-14AGS-210											39-28-8140	-14A-210	14			
				39-30-9125	5566-12AGS2-210	39-29-6128	5566-12AGS-210											39-28-8120	-12A-210	12			
				39-30-9105	5566-10AGS2-210	39-29-6108	5566-10AGS-210											39-28-8100	-10A-210	10			
G				39-30-9085	5566-08AGS2-210	39-29-6088	5566-08AGS-210	39-30-6082	5566-08AS-210									39-28-8080	-08A-210	8			
				39-30-9065	5566-06AGS2-210	39-29-6068	5566-06AGS-210	39-30-6062	5566-06AS-210									39-28-8060	-06A-210	6			
				39-30-9045	5566-04AGS2-210	39-29-6048	5566-04AGS-210	39-30-6042	5566-04AS-210									39-28-8040	-04A-210	4			
				39-30-9025	5566-02AGS2-210	39-29-6028	5566-02AGS-210											39-28-8020	5566-02A-210	2			
	EDP NO.	ENG. NO.		EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	CKT. SIZE	G		
	5566-NAPB-210			5566-NAGS2-210			5566-NAGS-210			5566-NAS-210			5566-NA-210										
				39-30-9244	5566-24AGS2	39-29-0243	5566-24AGS											39-28-1243	5566-24A	24			
				39-30-9224	5566-22AGS2														39-28-1223	5566-22A	22		
F				39-30-9204	5566-20AGS2	39-29-0203	5566-20AGS											39-28-1203	5566-20A	20			
				39-30-9184	5566-18AGS2	39-29-0183	5566-18AGS											39-28-1183	5566-18A	18			
				39-30-9164	5566-16AGS2													39-28-1163	5566-16A	16			
				39-30-9144	5566-14AGS2													39-28-1143	5566-14A	14			
				39-30-9124	5566-12AGS2	39-29-0123	5566-12AGS											39-28-1123	5566-12A	12	F		
				39-30-9104	5566-10AGS2	39-29-0103	5566-10AGS	39-30-6101	5566-10AS									39-28-1103	5566-10A	10			
				39-30-9084	5566-08AGS2	39-29-0083	5566-08AGS		5566-08AS									39-28-1083	5566-08A	8			
				39-30-9064	5566-06AGS2	39-29-0063	5566-06AGS											39-28-1063	5566-06A	6			
E				39-30-9044	5566-04AGS2	39-29-0043	5566-04AGS											39-28-1043	5566-04A	4			
				39-30-9024	5566-02AGS2	39-29-0023	5566-02AGS											39-28-1023	5566-02A	2			
	EDP NO.	ENG. NO.		EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	CKT. SIZE	E		
	5566-NAPB			5566-NAGS2			5566-NAGS			5566-NAS			5566-NA										

PARTS WITHOUT DRAIN HOLES

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#516558				molex					
IN/MM		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED)								MINI FIT JR VERTICAL HEADER ASSEMBLIES WITHOUT PEGS					
	MM	INCH											
4 PLACES	±	±											
3 PLACES	±	± 0.015		EC NO: 818232				PRODUCT CUSTOMER DRAWING					
2 PLACES	± 0.38	± 0.02		DRWN: VISHAH22025/02/25									
1 PLACE	± 0.5	±		CHK'D: GGA2025/04/22									
0 PLACES	±	±		APPR: GGA2025/04/22				DOCUMENT NUMBER SD-5566-002					
ANGULAR TOL ± 3.0 °				INITIAL REVISION:								DOC TYPE	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRWN: H.HIRAMOTO1989/04/03				PSD000M8					
				APPR: FSMITH2012/05/04									
THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE		5566		SEE TABLE		GENERAL MARKET		2 OF 5	

DOCUMENT STATUS	P1	RELEASE DATE	2025/04/22	05:23:44
-----------------	----	--------------	------------	----------

[illegible]

TRAY PACKED PART NUMBERS

PARTS WITHOUT DRAIN HOLES

TRAY PACKED PER TA 	46999-0137	5566-24AMS	TRAY PACKED PER TA 	46999-0149	5566-24AMS-210	24
	46999-0136	5566-22AMS		46999-0148	5566-22AMS-210	22
	46999-0135	5566-20AMS		46999-0147	5566-20AMS-210	20
	46999-0134	5566-18AMS		46999-0146	5566-18AMS-210	18
	46999-0133	5566-16AMS		46999-0145	5566-16AMS-210	16
	46999-0132	5566-14AMS		46999-0144	5566-14AMS-210	14
	46999-0131	5566-12AMS		46999-0143	5566-12AMS-210	12
	46999-0130	5566-10AMS		46999-0142	5566-10AMS-210	10
	46999-0129	5566-08AMS		46999-0141	5566-08AMS-210	8
	46999-0128	5566-06AMS		46999-0140	5566-06AMS-210	6
	46999-0127	5566-04AMS		46999-0139	5566-04AMS-210	4
	46999-0126	5566-02AMS		46999-0138	5566-02AMS-210	2
	EDP. NO.	ENG. NO.		EDP. NO.	ENG. NO.	CKT. SIZE
5566-NAMS			5566-NAMS-210			
						24
						22
						20
				39-53-9188	5566-18A-TA	18
						16
						14
						12
						10
						8
	46999-0630	5566-06AGS2-BL-TA				6
	46999-0629	5566-04AGS2-BL-TA				4
						2
	EDP NO.	ENG. NO.		EDP NO.	ENG. NO.	CKT. SIZE
	5566-NAGS2-BL-TA		5566-NA-TA			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

IN/MM

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.015
2 PLACES	± 0.38	± 0.02
1 PLACE	± 0.5	±
0 PLACES	±	±
ANGULAR TOL	± 3.0 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

CURRENT REV DESC: REMOVED OBSOLETE PART
NUMBERS AS PER PCN#516558

EC NO: 818232

DRWN: VISHAH2

CHK'D: GGA

APPR: GGA

2025/02/25

2025/04/22

2025/04/22

INITIAL REVISION:

DRWN: H.HIRAMOTO

APPR: FSMITH

1989/04/03

2012/05/04

mo

le

x

MINI FIT JR VERTICAL
HEADER ASSEMBLIES WITHOUT PEGS

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SD-5566-002

DOC TYPE

PSD

DOC PART

000

REVISION

M8

MATERIAL NUMBER

SEE TABLE


CUSTOMER

GENERAL MARKET

SHEET NUMBER

5 OF 5

THIRD ANGLE PROJECTION



DRAWING

C-SIZE

SERIES

5566

DOCUMENT STATUS	P1	RELEASE DATE	2025/04/22	05:23:44
-----------------	----	--------------	------------	----------

12

11

10

9

8

7

6

5

4

3

2

1

FORMS: Engage-master-to-ymc
REVISION: E1
DATE: 2025/05/01