

MATERIALS AND FINISHES:

MATERIALS AND FINISHES:

MATERIALS AND FINISHES:

PERFORMANCE REQUIREMENTS:

BNC PLUG STR CONNECTOR
MOLEX PN. 73174-0073

SMA PLUG STR CONNECTOR
MOLEX PN. 73251-0451

HEAT SHRINK TUBE: VERSAFIT
CABLE: RG316 OR EQUIVALENT

FREQUENCY RANGE: 0-6GHz
IMPEDANCE: 50 OHMS
WITHSTAND VOLTAGE(AC): 500V @0.5mA
CONTINUITY: 100% TEST

BODY, FERRULE, RETAINING RING,
WASHER & BUSHING: BRASS
PLATED: NICKEL

BODY: BRASS
PLATED: GOLD

COUPLING NUT: BRASS
PLATED: GOLD

CONTACT: BRASS
PLATED: GOLD

INSULATOR: PTFE

GASKET: SILICONE RUBBER

C-RING: BERYLLIUM COPPER

CRIMP TUBE: BRASS
PLATED: NICKEL

CENTER CONTACT: BRASS
PLATED: GOLD

INSULATOR & WASHER: PTFE

SPRING WASHER: BERYLLIUM COPPER
PLATED: NICKEL

COUPLING NUT: ZINC ALLOY
PLATED: NICKEL

GASKET: SILICONE RUBBER




TABLE:

PART NO.	DIM L		PACKAGING
	IN	MM	
73230-7006	39.370±.394	1000.00±10.00	PLASTIC BAG / POLY BAG
73230-7005	36.000±.394	914.40±10.00	
73230-7004	24.000±.394	609.60±10.00	
73230-7003	19.685±.394	500.00±10.00	
73230-7002	12.000±.394	304.80±10.00	
73230-7001	9.843±.197	250.00±5.00	
73230-7000	6.000±.197	152.40±5.00	

FUNCTIONAL SYMBOLS $\nabla_A = 0$ $\nabla_C = 0$ $\nabla_P = 0$ DIVISIONAL SYMBOLS 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: NEW RELEASE		
	DIMENSION UNITS	SCALE	<p>BNC PLUG STR TO SMA PLUG STR ON RG316</p> <p>PRODUCT SALES DRAWING</p>		
	MM/INCH	NTS			
	GENERAL TOLERANCES (UNLESS SPECIFIED)				
ANGULAR TOL ± 2'		STATUS: Production DRWN: Dennison J CHK'D: Karthik N Sathyanarayana APPR: Bharath Bharadwaj D			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	2023-10-26 2024-01-11 2024-01-11
			C-SIZE	73230	DOCUMENT NUMBER: 732307000 DOC TYPE: PSD DOC PART: 000 REVISION: A
		MATERIAL NUMBER: SEE TABLE		CUSTOMER: GENERAL MARKET	SHEET NUMBER: 1 OF 1