

MATERIALS AND FINISHES

BODY, COUPLING NUT SEE TABLE
PLATED SEE TABLE

CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON





GASKET SILICONE RUBBER

C RING BERYLLIUM COPPER


CRIMP TUBE BRASS
PLATED NICKEL

SHRINK TUBE
VERSAFIT 1/4


UL FILE E107635



CRIMP TUBE



SHRINK TUBE



RECOMMENDED CABLE STRIP

PS-89675-3460	ELECTRICAL/MECHANICAL
MIL-STD-348A, FIG. 310.1	INTERFACE
SPECIFICATION	DESCRIPTION

73251-0134	73251-0132 ONE PER BAG
73251-0133	STAINLESS STEEL / PASSIVATE (20 CAVITY TRAY)
73251-0132	BRASS / NICKEL PLATE (BULK PACK)
73251-0131	STAINLESS STEEL / PASSIVATE (BULK PACK)
PART NO.	DESCRIPTION

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		mm INCH	DRAWN BY DATE	TITLE				
▽=0	4 PLACES	± --- ± ---	SSS 2000/01/04	SMA PLUG, STR 50 OHMS, RG 58 SMA-PC				
▽=0	3 PLACES	± --- ± ---	CHECKED BY DATE					
	2 PLACES	± --- ± ---	SSS 2000/01/04					
	1 PLACE	± --- ± ---	APPROVED BY DATE					
	ANGULAR ± 2 °		GMH 2000/01/04	molex MOLEX INCORPORATED				
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-73251-013				SHEET NO. 1 OF 1
			SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

MATERIALS AND FINISHES

BODY, COUPLING NUT SEE TABLE
PLATED SEE TABLE

CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON





GASKET SILICONE RUBBER

C RING BERYLLIUM COPPER


CRIMP TUBE BRASS
PLATED NICKEL

SHRINK TUBE
VERSAFIT 1/4


UL FILE E107635



CRIMP TUBE



SHRINK TUBE



RECOMMENDED CABLE STRIP

PS-89675-3460	ELECTRICAL/MECHANICAL
MIL-STD-348A, FIG. 310.1	INTERFACE
SPECIFICATION	DESCRIPTION

73251-0134	73251-0132 ONE PER BAG
73251-0133	STAINLESS STEEL / PASSIVATE (20 CAVITY TRAY)
73251-0132	BRASS / NICKEL PLATE (BULK PACK)
73251-0131	STAINLESS STEEL / PASSIVATE (BULK PACK)
PART NO.	DESCRIPTION

CHG: 73251-0134
ADD 73251-0134
PS WAS 89675-1160
EC NO: URF2012-0421
2012/01/25
DRWN: JWIENER
CHKD: SSS
2012/01/25
APPR: JWIENER
2012/01/27
REV
A5

QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 2 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM/IN DRAWN BY DATE SSS 2000/01/04 CHECKED BY DATE SSS 2000/01/04 APPROVED BY DATE GMH 2000/01/04 MATERIAL NO. SEE TABLE SIZE C	SCALE DESIGN UNITS METRIC TITLE SMA PLUG, STR 50 OHMS, RG 58 SMA-PC MOLEX INCORPORATED SD-73251-013 DOCUMENT NO. SHEET NO. 1 OF 1	THIRD ANGLE PROJECTION
-------------------------------	--	---	--	---------------------------