

MATERIALS AND FINISHES

BODY, JAMNUT: BRASS
PLATED: GOLD


CENTER CONTACT: BERYLLIUM COPPER
PLATED: GOLD

LOCKWASHER: PHOSPHOR BRONZE
PLATED: GOLD



INSULATOR: TEFLON

SHRINK TUBE: ATUM OR EQUIVALENT



PACKAGING: BY TRAY




SMA JACK
INTERFACE
REVERSE
POLARITY





CRIMP TUBE





RECOMMENDED
PANEL CUTOUT




JAM NUT




LOCK WASHER



SHRINK TUBE



SOLDER
CONDUCTOR
& BRAID



0.80 MM CABLE
RECOMMENDED STRIP DIMS

PART # 73251-7010

CHG: ADD SOLDER
DESCRIPTION
PDR16082295
EC NO: URF2017-0140
DRWN:CWE102 2016/09/22
CHKD:
APPR:YCHENG 2016/10/13
REV DESCRIPTION

QUALITY
SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± --- ± ---
1 PLACE ± --- ± ---
0 PLACE ± --- ± ---
ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
CWE102 2016/08/09
CHECKED BY DATE
JOANNE 2016/08/09
APPROVED BY DATE
YCHENG 2016/09/14
MATERIAL NO.
732517010
SIZE
C

SCALE
DESIGN UNITS
METRIC
THIRD ANGLE
PROJECTION
TITLE
SMA JACK REVERSE POLAR
FOR 0.80MM CABLE,50 OHMS
SMA-JC
molex
DOCUMENT NO.
SD-73251-701
SHEET NO.
1 OF 1