


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	WFB	JTD	NO	12-13-12






RoHS COMPLIANT 515-1201F

Part Numbers with the "F" suffix ending are RoHS Compliant. Packaging is marked with "RoHS Compliant" label or equivalent markings.

NOTES:

1. DIALIGHT PART NUMBER 515-1201F
2. UNLESS OTHERWISE SPECIFIED, ALL SURFACES MUST HAVE FINISH OF SPI A3 TO B1.
3. MATERIAL TO BE CLEAR, TRANSMISSIBLE POLYCARBONATE (UL 94V-0 FLAMABILITY).
4. FLASH NOT TO EXCEED .005, SINK MARKS PERMISSIBLE ±.005.
5. UNLESS OTHERWISE SPECIFIED, .003" ROUNDS AND FILLETS PERMISSIBLE.
6. GATE VESTIGE TO BE .010" ABOVE OR BELOW SURFACE.
7. COMPONENTS DESIGNED TO BE PRESSED INTO PC BOARD.
8. UNLESS OTHERWISE SPECIFIED, 2 DEGREE DRAFT PERMISSIBLE.
9. * TOE-IN PERMISSIBLE BETWEEN LIMITS .310 TO .315
10. RECOMMENDED SURFACE MOUNT LED DIALIGHT PART NUMBER 597-77XX-2X7F OR EQUIVALENT P-LCC-4 PACKAGE.



THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.	
SCALE: 1.000	REV
ALL DIM'S IN: INCHES (MM)	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	
FRACTIONS: ±1/64	
DECIMALS (.XX): ±.01	
DECIMALS (.XXX): ±.010	
DECIMALS (.XXXX): ±.0005	
ANGLES: ±3°	
FINISH:	
Drawing Number	C-18000
Title	2 ELEMENT LIGHTPIPE 2.419" LENGTH
Material	
Dialight	1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727
FSCM	83330
Sheet	1 of 1
Family Table:	