









REV	ECN NO	REVISIONS	DRN	CKD	APP	QA	CM	DATE
A	97229	NEW RELEASE	LD		CS			9-6-22

- NOTES:
1. MATERIAL: COMPONENT TO BE MOLDED IN A CLEAR TRANSMISSIVE POLYCARBONATE.
 2. COMPONENT DESIGNED TO BE PRESSED INTO A P.C. BOARD.
 3. SUGGESTED DIALIGHT LEDs:
BI-COLOR LED: 597-77X1-5XXF
SINGLE COLOR LED: P/N 597-3XX2-507F, 597-3XX1-507F
 4. LIGHTPIPE REFERENCE DIALIGHT P/N 515-1126F.



SCALE 2.000



THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
DIALIGHT CORP. INTERNAL REFERENCE ONLY = 3D MODEL : 5151126-B.2		
SCALE: 1.000	DRAWING NUMBER	REV
ALL DIM's: INCH (mm)	C-18608	A
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE	
FRACTIONS: $\pm 1/64$	2 ELEMENT LIGHTPIPE	
DECIMALS (.XX): $\pm .01$	MATERIAL	
DECIMALS (.XXX): $\pm .005$	SEE NOTE 1	
DECIMALS (.XXXX): $\pm .0005$	FINISH	
ANGLES: $\pm 1^{\circ}$		
FSCM 83330	1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727 (732) 919-3119 www.dialight.com	
SHEET	I OF I	FAMILY TABLE: