






| REV | ECN NO | REVISIONS   | DRN | CKD | APP | QA | CM | DATE    |
|-----|--------|-------------|-----|-----|-----|----|----|---------|
| A   | 98121  | NEW RELEASE | LD  |     | CS  |    |    | 10-6-22 |



- NOTES:
1. COMPONENT TO BE MOLDED IN A CLEAR TRANSMISSIVE POLYCARBONATE.
  2. COMPONENT DESIGNED TO BE PRESSED INTO A P.C. BOARD.
  3. LIGHTSOURCE: RED/GREEN SMT BICOLOR LED (DIALIGHT P/N: 597-7701-5XXF).
  4. DIALIGHT PART NUMBER: 515-1097F.

|                                                                                                                                                                                                                                         |                                    |     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|-----|
| THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP. |                                    |     |
| DIALIGHT CORP INTERNAL REFERENCE ONLY - 3D MODEL: 99-102-ASST-B-2                                                                                                                                                                       |                                    |     |
| SCALE: 2.000                                                                                                                                                                                                                            | DRAWING NUMBER                     | REV |
| ALL DIM'S IN: INCHES (MM)                                                                                                                                                                                                               | C-18629                            | A   |
| TOLERANCES: UNLESS OTHERWISE SPECIFIED                                                                                                                                                                                                  | TITLE                              |     |
| FRACTIONS: ±1/64                                                                                                                                                                                                                        | 8-ELEMENT LIGHTPIPE (REF. 4 PAIRS) |     |
| DECIMALS (.XX): ±.01                                                                                                                                                                                                                    | MATERIAL                           |     |
| DECIMALS (.XXX): ±.005                                                                                                                                                                                                                  |                                    |     |
| DECIMALS (.XXXX): ±.0005                                                                                                                                                                                                                |                                    |     |
| ANGLES: ±1°                                                                                                                                                                                                                             |                                    |     |
| FINISH                                                                                                                                                                                                                                  |                                    |     |
| FSCM 83330                                                                                                                                                                                                                              |                                    |     |
| SHEET 1 OF 1                                                                                                                                                                                                                            | FAMILY TABLE:                      |     |