




DIALIGHT PART NUMBER	LED COLOR	LENS COLOR
521-8722F	YELLOW(590nm)	WATER CLEAR

REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	114070	NEW RELEASE	JSG	CS	NO	23JAN24



### RECOMMENDED PCB LAYOUT

#### NOTES:

1. LEAD SPACING MEASURED NEAR EPOXY PACKAGE.
2. LEDS TO BE PACKAGED IN A TRANSPARENT STATIC SHIELDED METAL FOIL BAG WITH ESD LABELING OR EQUIVALENT
3. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS) MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING AND STORAGE IN ACCORDANCE WITH IPC-610
4. THIS PRODUCT IS ROHS COMPLIANT, EACH BAG IS MARKED WITH ROHS COMPLIANT LABEL OR EQUIVALENT MARKINGS. LED MUST BE PB FREE (ROHS COMPLIANT).
5. SOLDERING : LEAVE A MINIMUM OF 2mm CLEARANCE FROM THE BASE OF THE LENS TO THE SOLDERING POINT.

ABSOLUTE MAXIMUM RATINGS AT 25°C						
LED COLOR	POWER DISSIPATION (mW)	FORWARD CURRENT (mA)	PEAK FORWARD CURRENT (mA)	OPERATING TEMPRATURE (°C)	STORAGE TEMPRATURE (°C)	REVERSE VOLTAGE (V)
YELLOW	75	30	50 (1/10 DUTY CYCLE, 0.1ms PULSE WIDTH)	-40°C TO +85°C	-40°C TO +85°C	5

OPERATING CHARACTERISTICS AT 25°C AMBIENT									
LED COLOR	TEST CONDITION (mA)	LUMINOUS INTENSITY (mcd)		FORWARD VOLTAGE (V)		REVERSE CURRENT (uA)	VIEWING ANGLE (DEGREES)	DOMINANT WAVELENGTH (nm)	
		MIN	MAX	MIN	MAX			MAX	MIN
YELLOW	20mA	4800	11800	1.8	2.4	10µA @ VR=5V	30	584	594

CATHODE  ANODE

LED SCHEMATIC



**ATTENTION:**  
OBSERVE PRECAUTIONS FOR  
HANDLING ELECTROSTATIC  
SENSITIVE DEVICES

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.
DIALIGHT CORP INTERNAL REFERENCE ONLY : 3D MODEL : 450521500X18-A.4
SCALE: 2.000
ALL DIM's: INCH (mm)
TOLERANCES: UNLESS OTHERWISE SPECIFIED
FRACTIONS: (.XX): ±.01
DECIMALS (.XXX): ±.005
DECIMALS (.XXXX): ±.0005
ANGLES: ±1°
FINISH
DRAWING NUMBER
C-18737
REV
A
TITLE
5mm HIGH INTENSITY YELLOW
MATERIAL
Dialight
1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727 (732) 919-3119 www.dialight.com
FSCM 83330
SHEET 1 OF 1 FAMILY TABLE