


DGF-G-212J (20.07)


E
D
C
B
A

890131PS
(ON DIMYARD)台異図




NOTE1. SHAERED AREA HAS NO PLATING.
NOTE2. APPLICABLE WIRES; STRANDED CONDUCTORS
CORE TYPE: 4.0sq
STANDARD OVERALL DIAMETER: $\phi 3.4$ to 3.7mm
NOTE3. THE FOLLOWING INFORMATION SHOULD BE SHOWED ON THE IDENTIFICATION LABEL.
PRODUCT NAME: MX81S17H1F1
QTY : 1,700
NOTE4. IDENTIFICATION MARK "X" IS MARKED.
NOTE5. REFER TO JAHL-11557-1 ABOUT CRIMP SPECIFICATIONS.

注1. せん断面にめっきは無い。
注2. 適用電線は導外断面積: 4.0sqかつ被覆外形 $\phi 3.4 \sim 3.7\text{mm}$ の撚り線とする。
注3. 下記情報を現品票に表示する。
製品名: MX81S17H1F1
数量 : 1,700
注4. バレル識別マーク"X"を本箇所刻印する。
注5. 圧着仕様はJAHL-11557-1を参照すること。



【REF.】 ISOMETRIC VIEW
【参考】 製品斜視図

版数 VER.	年月日 DATE	CN NO.	変更内容 DESCRIPTION	製図 DR.	担当 CHK.	査閲 APPD.	承認 APPD.
------------	-------------	--------	---------------------	-----------	------------	-------------	-------------



3	MX81 POWER SOCKET TERMINAL	1,700	COPPER ALLOY	TIN PLATING	—
2	INTERLAYERED TAPE	1	PAPER	—	—
1	REEL	1	CARDBOARD	—	—
符号 NO.	名称 DESCRIPTION	個数 QTY.	材料 MATERIAL	仕上 FINISH	図番 DWG NO.

仕様書 (SPECIFICATION) JACS-11557 JAHL-11557, JAHL-11557-1		第1版 (ORIGINAL DATE) 30/MAY/2025		尺度 (SCALE) 1/5		シリーズ (SERIES) MX81		日本航空電子工業株式会社	
一般公差 (GENERAL TOLERANCE)		製図 DR.		名称 (TITLE) MX81S17H1F1		JAE		JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	
寸法 (DIMENSION)		担当 CHK.		質量 (MASS) (0.37g/pc)		図面番号 (DRAWING NO.) SJ131063		版数 (VER.) 1	
角度 (ANGLES)		査閲 APPD.		シートの (SHEET NO.) 1 OF 1		S/W			
単位 (UNIT) : mm		承認 APPD.							