

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), two red LC duplex adapters labeled TAP, four blue LC duplex adapters labeled LIVE

CORNING

Part Number: ETM-5A-G

EDGE Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets. The Edge Tap Module enables passive optical tapping of the network while reducing downtime and link loss, and increasing rack space utilization and density.

Features and Benefits

Designed for Duplex based infrastructure solutions

Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), two red LC duplex adapters labeled TAP, four blue LC duplex adapters labeled LIVE



EDGE™ Solutions Tap Module, Single-mode (OS2), 50/50 split ratio (live/tap), two red LC duplex adapters labeled TAP, four blue LC duplex adapters labeled LIVE

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), two red LC duplex adapters labeled TAP, four blue LC duplex adapters labeled LIVE

CORNING

Specifications

General Specifications

Product Type	Modules
Fiber Category	Single-mode (OS2)
Application	Data Center

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Design

Fiber Count	4
Adapter Color Front	Blue / Red
Adapter Type Front	Shuttered LC
Housing Type	Modules
Color	Gray
Number of Ports	4
Number of Adapters per Panel	2

Cable Design

Fiber Count	4
Polarity	Straight-Through, TIA-568 Type-A

Optical Specification - Hardware

Split Ratio Live/Tap	50/50
Splitter Loss for Tap Modules	3.6 dB LIVE / 3.6 dB TAP
Fiber Category	Single-mode (OS2)

EDGE™ Tap Module Single-mode (OS2), 50/50 split ratio (live/tap), two red LC duplex adapters labeled TAP, four blue LC duplex adapters labeled LIVE

CORNING

Specifications - Connector A

Connector Type	LC duplex
Ferrule Material	Ceramic

Specifications - Connector B

Connector Type	LC duplex
Ferrule Material	Ceramic

Dimensions

Height	12 mm (0.47 in)
Width	191 mm (7.52 in)
Depth	152 mm (5.98 in)

Ordering Information

Product Number	ETM-5A-G
Units per Delivery	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.