



FOR CUSTOMER APPROVAL ONLY			REV	BY	DATE	COMMENT
NAME:	0	CG	07/01/20	RELEASE DATE		
TITLE:						
DATE:				PROPRIETARY AND CONFIDENTIAL		
				THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INNOVATIVE COMPONENTS. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF INNOVATIVE COMPONENTS IS PROHIBITED.		
SIGNATURE:						

DIMENSIONS ARE IN INCHES		DRAWN	VIRR	INNOVATIVE COMPONENTS	
TOLERANCES		APPROVED	LQR	PART NAME	
FRACTIONAL $\pm$		DATE	07/01/2020	2.5" Soft touch fluted knob	
TWO PLACE DECIMAL $\pm 0.03$		COMMENTS		5/16-18 x 2" Steel, Zinc Stud	
THREE PLACE DECIMAL $\pm 0.010$		Soft Touch			
UNLESS OTHERWISE NOTED		Material Usage: 0.0291 Pounds			
INNER PART NUMBER		RoHS Compliant			
KN5C2000F6--21					
MATERIAL	INSERT PART NUMBER		PART NUMBER		DRAWING NUMBER
TPE-48 Shore A	Steel		KN5C2000F7S--21		KN5C2000F7S--21-RO
FINISH	INSERT FINISH				
Textured	Trivalent Zinc				SCALE 1:1.5



PLASTIC KNOBS / CONTROL KNOBS / HANDLES / QUICK RELEASE PINS & BALL LOCK PINS  
SPRING LOADED PINS & PLUNGERS / WIRE ROPE LANYARDS / THREAD IDENTIFIERS