


1. SPECIFICATION

ADI-1005S-C-1


ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	5.0	
02	Operating Voltage	V	4.0 ~ 7.0	
03	Consumption Current	mA (Max)	30	Rated Voltage
04	Resonant Frequency	Hz	2700 ± 300	Rated Voltage

REV NO.

REVISION NOTE

APPROVAL

DATE



RECOMMENDED PCB LAYOUT

TITLE: SOUND TRANSDUCER (SMD)

DRAWN: Moose

2017/07/14

SCALE: 1:1

SHEET: 1 : 1

PART NO. ADI-1005S-C-1

DESIGNED: R & D OF AAT

UNITS: mm

DWG NO. BMC9650S-0527)

1

CHECKED:

TOLERANCE ± 0.5

APPROVAL:

UNLESS OTHERWISE SPECIFIED:

ONE PLACE DECIMAL ± ***

TWO PLACE DECIMAL ± ***

THREE PLACE DECIMAL ± ***

REV

MATERIAL: LCP



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC