



1. SPECIFICATION

AD-52A3F

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	3	 Standard state, standard drive circuit. Square wave 1/2 duty.
02	Operating Voltage	V	2 ~ 4.35	
03	Consumption Current	mA Max.	110	
04	Sound pressure level (Distance at 10cm)	dB(A) Min.	72	Rated voltage, rated frequency.
05	Direct Current Resistance	Ω	12 ± 3	
06	Rated Frequency	Hz	4000	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



PCB LAYOUT

RoHS

TITLE: SOUND TRANSDUCER (SMD)		DRAWN: Zack	2019/08/30	SCALE: 1:1	SHEET: 1 : 1
PART NO. AD-52A3F		DESIGNED: R & D OF AAT		UNITS: mm	
DWG NO.		CHECKED:		TOLERANCE ± 0.5	
FDM-2810 SMD-050020F-03040N		APPROVAL:		UNLESS OTHERWISE SPECIFIED:	
REV 1		MATERIAL: LCP		ONE PLACE DECIMAL ± ***	
				TWO PLACE DECIMAL ± ***	
				THREE PLACE DECIMAL ± ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC