
1. SPECIFICATION

AR-150632-2P

ITEM		SPECIFICATIONS
01	**Type**	Dynamic 15 x 6mm receiver unit
02	**Sound pressure level**	106 dB ±3 dB at 1KHz 179mV with IEC318 coupler.
03	**Impedance**	32 **Ω**±15% 1 KHz
04	**Frequency Range**	300 ~ 7 KHz
05	**Rated Input Power**	20m W
06	**Max. Input Power**	30m W
07	**Total Harmonics Distortion**	Max 10 % at 1 KHz, 1.79m V

AIC

REV NO.	REVISION NOTE	APPROVAL	DATE



RoHS

TITLE: DYNAMIC RECEIVER		DRAWN: Moose 2015/09/02	SCALE: 4:1	SHEET: 1:1
		DESIGNED: R&D OF AAT	UNITS: mm	
PART NO. AR-150632A-2P	1	CHECKED:	TOLERANCE ± 0.5	
		APPROVAL:	UNLESS OTHERWISE SPECIFIED: ONE PLACE DECIMAL ± *** TWO PLACE DECIMAL ± *** THREE PLACE DECIMAL ± ***	
DWG NO. UGRP150632-16T-02	REV	MATERIAL: PPA		

ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC