



Insulated Universal Combination Pliers, 8-Inch



Be protected from up to 1,000 volts of electric current when working near energized sources with Klein's 8-Inch Insulated Universal Combination Pliers. These pliers offer flame-retardant handles, a toothed pipe grip and a high-leverage design, with the rivet closer to the cutting edge for 40% greater cutting and gripping power than other pliers designs. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools.

Specifications

Type:	High-Leverage Pliers	Application:	Cuts ACSR, Screws, Nails and Most Hardened Wires
Special Features:	Integral Guards Help Prevent Hand Contact With Conductive Parts	Overall Length:	8.76" (22.3 cm)
Material:	Induction Hardened Steel	Nose Type:	Universal
Jaw Length:	1.78" (4.5 cm)	Jaw Width:	1.02" (2.6 cm)
Jaw Thickness:	0.55" (1.4 cm)	Knife Length:	0.711" (1.8 cm)
Cut Style:	Side-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	4.93" (12.5 cm)	Insulated:	Yes
Standards:	IEC 60900 and ASTM F1505	Weight:	1.0 lb (0.5 kg)