



Haven's® Grip with Swing Latch



Klein Tools' 1604 Series Messenger and Guy Strand Haven's® Grips are designed for use when a light, compact grip is desired, and where cable deformation is not a factor. They are recommended for use with steel strand cables. All Klein grips are manufactured from custom drop-forged steel that is machined and heat treated for excellent durability. Each grip is individually hand inspected and actuated for proper function. Grips are also rigorously tested and pulled to rated load to ensure the highest quality and reliability.

Specifications

Type:	Haven's Grip	Application:	Wire Pulling
Overall Length (Inch):	8.75	Overall Length (cm):	22.2
Overall Height (Inch):	3.88	Overall Height (cm):	9.9
Overall Width (Inch):	1.75	Overall Width (cm):	4.4
Material:	Steel	Cable Type:	EHS, Guy Strand, Messenger
Cable Diameter:	0.125" to 0.5" (3.18 to 12.7 mm)	Hot Latch:	No
Swing Latch:	Yes	Spring:	No
Locking Handle:	No	Teeth Type:	Aggressive
Jaw Length (Inch):	0.25	Jaw Length (cm):	0.6
Jaw Type:	Curved	Maximum Safe Load (lb):	5000
Maximum Safe Load (kg):	2268	Weight (lb):	2.6
Weight (kg):	1.2		